

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270985

Luminaire Tested: P3AS02R409827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 60.0 lumens
Efficiency: N/A
Efficacy: 16.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270985

CATALOG NUMBER: P3AS02R409827DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270985

CATALOG NUMBER: P3AS02R409827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18683
5°	18314
10°	17034
15°	14847
20°	11971
25°	8976
30°	6305
35°	4122
40°	2490
45°	1489
50°	887
55°	726
60°	658
65°	571
70°	513
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1489 cd/sqm

TEST NUMBER: P1270985

CATALOG NUMBER: P3AS02R409827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.7	12.9
10°-20°	18.0	30.1
20°-30°	17.0	28.3
30°-40°	9.8	16.4
40°-50°	3.9	6.5
50°-60°	1.7	2.9
60°-70°	1.1	1.8
70°-80°	0.6	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	42.7	71.2
0°-40°	52.5	87.6
0°-60°	58.2	97.0
0°-90°	60.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	60.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	85	
5°	83	8
15°	65	18
25°	37	17
35°	15	10
45°	5	4
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1270985

CATALOG NUMBER: P3AS02R409827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	85.2
2.5°	84.7
5°	83.2
7.5°	80.3
10°	76.5
12.5°	71.5
15°	65.4
17.5°	58.7
20°	51.3
22.5°	43.9
25°	37.1
27.5°	30.7
30°	24.9
32.5°	19.8
35°	15.4
37.5°	11.7
40°	8.7
42.5°	6.5
45°	4.8
47.5°	3.5
50°	2.6
52.5°	2.1
55°	1.9
57.5°	1.7
60°	1.5
62.5°	1.2
65°	1.1
67.5°	0.9
70°	0.8
72.5°	0.7
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)