

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270995

Luminaire Tested: P3AS02R459827DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459827DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 223.0 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270995

CATALOG NUMBER: P3AS02R459827DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1270995

CATALOG NUMBER: P3AS02R459827DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	90	89
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86	85	84
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	81	80
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	78	77
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	74	73
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	71	70
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	65	64
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96681
5°	97204
10°	94209
15°	78956
20°	60345
25°	36728
30°	15293
35°	4899
40°	1517
45°	310
50°	239
55°	268
60°	219
65°	259
70°	192
75°	254
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 336 cd/sqm

TEST NUMBER: P1270995

CATALOG NUMBER: P3AS02R459827DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	18.7
10°-20°	95.6	42.9
20°-30°	68.8	30.9
30°-40°	14.3	6.4
40°-50°	1.3	0.6
50°-60°	0.6	0.3
60°-70°	0.4	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.0	92.4
0°-40°	220.4	98.8
0°-60°	222.2	99.7
0°-90°	223.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	223.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	441	
5°	442	42
15°	348	96
25°	152	69
35°	18	14
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270995

CATALOG NUMBER: P3AS02R459827DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	440.9
2.5°	441.1
5°	441.6
7.5°	438.4
10°	423.1
12.5°	391.2
15°	347.8
17.5°	303.4
20°	258.6
22.5°	207.2
25°	151.8
27.5°	100.1
30°	60.4
32.5°	33.8
35°	18.3
37.5°	10.3
40°	5.3
42.5°	2.3
45°	1.0
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)