

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270306

Luminaire Tested: P3AS17R559740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 666.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270306
CATALOG NUMBER: P3AS17R559740DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1270306
 CATALOG NUMBER: P3AS17R559740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75				75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182880
5°	181025
10°	174813
15°	161590
20°	139429
25°	110135
30°	78113
35°	50380
40°	30257
45°	17056
50°	9177
55°	3288
60°	2938
65°	2854
70°	2757
75°	2626
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17056 cd/sqm



TEST NUMBER: P1270306
 CATALOG NUMBER: P3AS17R559740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	11.6
10°-20°	196.8	29.6
20°-30°	206.3	31.0
30°-40°	120.3	18.1
40°-50°	45.0	6.8
50°-60°	10.6	1.6
60°-70°	5.4	0.8
70°-80°	3.2	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.4	72.1
0°-40°	600.8	90.2
0°-60°	656.4	98.6
0°-90°	666.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	834	
5°	822	77
15°	712	197
25°	455	206
35°	188	120
45°	55	45
55°	9	11
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1270306
CATALOG NUMBER: P3AS17R559740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	834.0
2.5°	831.5
5°	822.4
7.5°	807.7
10°	785.1
12.5°	753.3
15°	711.8
17.5°	659.3
20°	597.5
22.5°	528.5
25°	455.2
27.5°	380.0
30°	308.5
32.5°	243.8
35°	188.2
37.5°	143.0
40°	105.7
42.5°	75.8
45°	55.0
47.5°	39.7
50°	26.9
52.5°	15.3
55°	8.6
57.5°	7.3
60°	6.7
62.5°	6.1
65°	5.5
67.5°	4.9
70°	4.3
72.5°	3.7
75°	3.1
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)