

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270325

Luminaire Tested: P3AS17R609740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1612.9 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270325

CATALOG NUMBER: P3AS17R609740DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1270325

CATALOG NUMBER: P3AS17R609740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	385167
5°	369887
10°	380844
15°	385746
20°	340603
25°	287049
30°	232795
35°	151621
40°	69645
45°	26700
50°	8938
55°	2370
60°	2193
65°	1920
70°	1603
75°	2118
80°	1515
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26700 cd/sqm

TEST NUMBER: P1270325

CATALOG NUMBER: P3AS17R609740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	10.0
10°-20°	465.3	28.8
20°-30°	542.7	33.6
30°-40°	350.2	21.7
40°-50°	78.5	4.9
50°-60°	7.8	0.5
60°-70°	3.7	0.2
70°-80°	2.1	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.8	72.5
0°-40°	1520.0	94.2
0°-60°	1606.3	99.6
0°-90°	1612.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1612.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1756	
5°	1680	162
15°	1699	465
25°	1186	543
35°	566	350
45°	86	78
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1270325

CATALOG NUMBER: P3AS17R609740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1756.5
2.5°	1727.8
5°	1680.4
7.5°	1677.9
10°	1710.4
12.5°	1731.6
15°	1699.2
17.5°	1601.8
20°	1459.6
22.5°	1311.2
25°	1186.4
27.5°	1064.2
30°	919.4
32.5°	749.8
35°	566.4
37.5°	386.7
40°	243.3
42.5°	146.0
45°	86.1
47.5°	49.9
50°	26.2
52.5°	8.7
55°	6.2
57.5°	5.0
60°	5.0
62.5°	3.7
65°	3.7
67.5°	3.7
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)