

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271112

Luminaire Tested: P3AS02R659827DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271112  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R659827DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 199.0 lumens  
Efficiency: N/A  
Efficacy: 55.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271112  
CATALOG NUMBER: P3AS02R659827DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1271112  
 CATALOG NUMBER: P3AS02R659827DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53329
5°	49505
10°	47873
15°	46152
20°	42657
25°	38857
30°	30030
35°	17400
40°	6899
45°	2946
50°	682
55°	76
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2946 cd/sqm



TEST NUMBER: P1271112  
 CATALOG NUMBER: P3AS02R659827DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.2	10.7
10°-20°	56.6	28.5
20°-30°	71.7	36.0
30°-40°	40.8	20.5
40°-50°	8.1	4.1
50°-60°	0.4	0.2
60°-70°	0.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.5	75.1
0°-40°	190.4	95.6
0°-60°	198.9	99.9
0°-90°	199.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	199.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	243	
5°	225	21
15°	203	57
25°	161	72
35°	65	41
45°	10	8
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1271112  
CATALOG NUMBER: P3AS02R659827DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	243.2
1°	241.4
2°	237.4
3°	232.9
4°	228.4
5°	224.9
6°	222.4
7°	220.4
8°	218.6
9°	216.8
10°	215.0
11°	213.2
12°	211.2
13°	208.8
14°	206.3
15°	203.3
16°	199.7
17°	195.7
18°	191.5
19°	187.0
20°	182.8
21°	178.6
22°	174.7
23°	170.7
24°	166.0
25°	160.6
26°	154.2
27°	146.4
28°	137.7
29°	128.3
30°	118.6
31°	107.9
32°	97.3
32.5°	91.8
33°	86.5
34°	75.7
35°	65.0
36°	55.2
37°	45.5
37.5°	40.5
38°	36.5
39°	29.5
40°	24.1
42.5°	14.9
45°	9.5



TEST NUMBER: P1271112  
CATALOG NUMBER: P3AS02R659827DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	5.6
50°	2.0
52.5°	0.4
55°	0.2
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)