

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270376

Luminaire Tested: P3AS17R659740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 424.0 lumens
Efficiency: N/A
Efficacy: 20.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270376

CATALOG NUMBER: P3AS17R659740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270376

CATALOG NUMBER: P3AS17R659740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107776
5°	105084
10°	97861
15°	87696
20°	75747
25°	63004
30°	49679
35°	36808
40°	25362
45°	15723
50°	8563
55°	5390
60°	4561
65°	4099
70°	3526
75°	3135
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15723 cd/sqm

TEST NUMBER: P1270376

CATALOG NUMBER: P3AS17R659740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	10.5
10°-20°	107.4	25.3
20°-30°	118.7	28.0
30°-40°	86.2	20.3
40°-50°	40.4	9.5
50°-60°	13.6	3.2
60°-70°	7.8	1.9
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.5	63.8
0°-40°	356.7	84.1
0°-60°	410.7	96.9
0°-90°	424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	477	44
15°	386	107
25°	260	119
35°	138	86
45°	51	40
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1270376

CATALOG NUMBER: P3AS17R659740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	491.5
2.5°	488.4
5°	477.4
7.5°	460.9
10°	439.5
12.5°	414.5
15°	386.3
17.5°	355.8
20°	324.6
22.5°	292.2
25°	260.4
27.5°	228.0
30°	196.2
32.5°	165.7
35°	137.5
37.5°	111.9
40°	88.6
42.5°	67.9
45°	50.7
47.5°	36.7
50°	25.1
52.5°	17.1
55°	14.1
57.5°	12.2
60°	10.4
62.5°	9.2
65°	7.9
67.5°	6.7
70°	5.5
72.5°	4.9
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)