

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270392

Luminaire Tested: P3AS17R709740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1488.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270392
CATALOG NUMBER: P3AS17R709740DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1270392
 CATALOG NUMBER: P3AS17R709740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289341
5°	272815
10°	258690
15°	254031
20°	244858
25°	230820
30°	229175
35°	199591
40°	129099
45°	61030
50°	8563
55°	688
60°	526
65°	623
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61030 cd/sqm



TEST NUMBER: P1270392
 CATALOG NUMBER: P3AS17R709740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	7.8
10°-20°	314.3	21.1
20°-30°	444.6	29.9
30°-40°	446.8	30.0
40°-50°	160.7	10.8
50°-60°	4.3	0.3
60°-70°	1.0	0.1
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.5	58.8
0°-40°	1321.3	88.8
0°-60°	1486.3	99.9
0°-90°	1488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1320	
5°	1239	116
15°	1119	314
25°	954	445
35°	746	447
45°	197	161
55°	2	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1270392
CATALOG NUMBER: P3AS17R709740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1319.5
1°	1315.8
2°	1304.2
3°	1285.8
4°	1262.6
5°	1239.4
6°	1217.4
7°	1200.3
8°	1185.0
9°	1172.8
10°	1161.8
11°	1152.6
12°	1144.1
13°	1135.5
14°	1127.6
15°	1119.0
16°	1108.6
17°	1097.6
18°	1084.2
19°	1067.7
20°	1049.3
21°	1029.2
22°	1009.0
23°	989.4
24°	970.5
25°	954.0
26°	942.4
27°	933.2
28°	925.9
29°	917.3
30°	905.1
31°	887.4
32°	862.3
32.5°	848.3
33°	829.3
34°	792.0
35°	745.6
36°	694.3
37°	636.2
37.5°	609.3
38°	572.6
39°	507.2
40°	451.0
42.5°	312.3
45°	196.8



TEST NUMBER: P1270392
CATALOG NUMBER: P3AS17R709740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	105.7
50°	25.1
52.5°	3.1
55°	1.8
57.5°	1.8
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)