

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271125

Luminaire Tested: P3AS02R659827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 131.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271125

CATALOG NUMBER: P3AS02R659827DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271125

CATALOG NUMBER: P3AS02R659827DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23310
5°	23002
10°	22222
15°	20954
20°	19345
25°	17541
30°	15547
35°	13224
40°	10534
45°	7443
50°	4298
55°	2370
60°	2193
65°	1972
70°	1795
75°	1694
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7443 cd/sqm

TEST NUMBER: P1271125

CATALOG NUMBER: P3AS02R659827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.8	7.5
10°-20°	25.8	19.7
20°-30°	33.2	25.3
30°-40°	30.7	23.4
40°-50°	18.5	14.2
50°-60°	6.3	4.8
60°-70°	3.8	2.9
70°-80°	2.2	1.7
80°-90°	0.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	68.8	52.6
0°-40°	99.6	76.0
0°-60°	124.4	95.0
0°-90°	131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	106	
5°	104	10
15°	92	26
25°	72	33
35°	49	31
45°	24	19
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1271125

CATALOG NUMBER: P3AS02R659827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	106.3
2.5°	105.8
5°	104.5
7.5°	102.5
10°	99.8
12.5°	96.5
15°	92.3
17.5°	87.8
20°	82.9
22.5°	77.7
25°	72.5
27.5°	67.0
30°	61.4
32.5°	55.7
35°	49.4
37.5°	43.3
40°	36.8
42.5°	30.3
45°	24.0
47.5°	18.1
50°	12.6
52.5°	8.0
55°	6.2
57.5°	5.5
60°	5.0
62.5°	4.3
65°	3.8
67.5°	3.3
70°	2.8
72.5°	2.5
75°	2.0
77.5°	1.7
80°	1.2
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)