

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270462

Luminaire Tested: P3AS20R159740D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159740D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1292.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270462

CATALOG NUMBER: P3AS20R159740D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270462

CATALOG NUMBER: P3AS20R159740D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325895
5°	317036
10°	289730
15°	253781
20°	217719
25°	181777
30°	145465
35°	109111
40°	79177
45°	51757
50°	32374
55°	21906
60°	19384
65°	17849
70°	16798
75°	15250
80°	14522
85°	12328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51757 cd/sqm

TEST NUMBER: P1270462

CATALOG NUMBER: P3AS20R159740D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.9	10.3
10°-20°	311.5	24.1
20°-30°	343.2	26.6
30°-40°	257.0	19.9
40°-50°	133.2	10.3
50°-60°	55.2	4.3
60°-70°	34.2	2.6
70°-80°	19.2	1.5
80°-90°	5.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.6	61.0
0°-40°	1044.6	80.9
0°-60°	1233.0	95.4
0°-90°	1292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1486	
5°	1440	133
15°	1118	311
25°	751	343
35°	408	257
45°	167	133
55°	57	55
65°	34	34
75°	18	19
85°	5	6
90°	0	

TEST NUMBER: P1270462

CATALOG NUMBER: P3AS20R159740D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1486.2
1°	1487.8
2°	1482.9
3°	1473.1
4°	1458.4
5°	1440.3
6°	1417.4
7°	1392.9
8°	1363.4
9°	1332.3
10°	1301.2
12.5°	1211.2
15°	1117.9
17.5°	1024.6
20°	933.0
22.5°	839.7
25°	751.3
27.5°	662.9
30°	574.5
32.5°	487.8
35°	407.6
37.5°	338.8
40°	276.6
42.5°	219.3
45°	166.9
47.5°	126.0
50°	94.9
52.5°	70.4
55°	57.3
57.5°	50.7
60°	44.2
62.5°	39.3
65°	34.4
67.5°	29.5
70°	26.2
72.5°	21.3
75°	18.0
77.5°	14.7
80°	11.5
82.5°	8.2
85°	4.9
87.5°	1.6
90°	0.0

(END OF REPORT)