

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271205

Luminaire Tested: P3AS05R209827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 133.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271205

CATALOG NUMBER: P3AS05R209827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271205

CATALOG NUMBER: P3AS05R209827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32892
5°	32027
10°	29458
15°	25925
20°	22239
25°	18678
30°	15091
35°	11484
40°	8187
45°	5396
50°	3343
55°	2179
60°	2017
65°	1816
70°	1731
75°	1610
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5396 cd/sqm

TEST NUMBER: P1271205

CATALOG NUMBER: P3AS05R209827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.5	10.1
10°-20°	31.8	23.9
20°-30°	35.3	26.5
30°-40°	26.9	20.2
40°-50°	13.8	10.4
50°-60°	5.7	4.3
60°-70°	3.5	2.6
70°-80°	2.0	1.5
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.5	60.6
0°-40°	107.5	80.8
0°-60°	126.9	95.4
0°-90°	133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	150	
5°	146	13
15°	114	32
25°	77	35
35°	43	27
45°	17	14
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1271205

CATALOG NUMBER: P3AS05R209827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	150.0
1°	150.2
2°	149.5
3°	148.7
4°	147.3
5°	145.5
6°	143.3
7°	140.9
8°	138.4
9°	135.3
10°	132.3
12.5°	123.5
15°	114.2
17.5°	104.7
20°	95.3
22.5°	85.8
25°	77.2
27.5°	68.6
30°	59.6
32.5°	51.2
35°	42.9
37.5°	35.6
40°	28.6
42.5°	22.5
45°	17.4
47.5°	13.2
50°	9.8
52.5°	7.3
55°	5.7
57.5°	5.2
60°	4.6
62.5°	4.1
65°	3.5
67.5°	3.0
70°	2.7
72.5°	2.2
75°	1.9
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)