

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270546

Luminaire Tested: P3AS20R309740D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309740D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1734.0 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270546

CATALOG NUMBER: P3AS20R309740D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270546

CATALOG NUMBER: P3AS20R309740D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1011849
5°	963062
10°	810072
15°	584203
20°	362375
25°	206093
30°	114473
35°	62265
40°	32833
45°	17769
50°	9484
55°	6270
60°	5745
65°	5967
70°	5257
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17769 cd/sqm

TEST NUMBER: P1270546

CATALOG NUMBER: P3AS20R309740D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.0	22.7
10°-20°	700.3	40.4
20°-30°	404.7	23.3
30°-40°	153.6	8.9
40°-50°	47.1	2.7
50°-60°	15.9	0.9
60°-70°	10.8	0.6
70°-80°	5.8	0.3
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1499.0	86.4
0°-40°	1652.6	95.3
0°-60°	1715.6	98.9
0°-90°	1734.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1734.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4614	
5°	4375	394
15°	2573	700
25°	852	405
35°	233	154
45°	57	47
55°	16	16
65°	12	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1270546

CATALOG NUMBER: P3AS20R309740D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4614.4
1°	4611.1
2°	4583.3
3°	4530.8
4°	4465.3
5°	4375.2
6°	4260.6
7°	4132.8
8°	3990.3
9°	3819.9
10°	3638.1
11°	3441.5
12°	3233.5
13°	3015.6
14°	2794.5
15°	2573.4
17.5°	2029.5
20°	1552.9
22.5°	1151.5
25°	851.8
27.5°	619.2
30°	452.1
32.5°	326.0
35°	232.6
37.5°	162.2
40°	114.7
42.5°	80.3
45°	57.3
47.5°	39.3
50°	27.8
52.5°	19.7
55°	16.4
57.5°	14.7
60°	13.1
62.5°	11.5
65°	11.5
67.5°	9.8
70°	8.2
72.5°	6.6
75°	4.9
77.5°	4.9
80°	3.3
82.5°	3.3
85°	1.6
87.5°	0.0



TEST NUMBER: P1270546

CATALOG NUMBER: P3AS20R309740D010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)