

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271269

Luminaire Tested: P3AS05R309827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271269

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271269

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66376
5°	64891
10°	60342
15°	53689
20°	46181
25°	39123
30°	32486
35°	25484
40°	18263
45°	11970
50°	6823
55°	4473
60°	4254
65°	3943
70°	3526
75°	3219
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11970 cd/sqm

TEST NUMBER: P1271269

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.4	9.7
10°-20°	65.8	23.4
20°-30°	74.1	26.4
30°-40°	59.2	21.1
40°-50°	30.4	10.8
50°-60°	11.4	4.1
60°-70°	7.5	2.7
70°-80°	4.0	1.4
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.2	59.5
0°-40°	226.4	80.6
0°-60°	268.3	95.5
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	303	
5°	295	27
15°	236	66
25°	162	74
35°	95	59
45°	39	30
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1271269

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	302.7
1°	302.7
2°	301.7
3°	300.0
4°	297.6
5°	294.8
6°	291.4
7°	286.9
8°	282.1
9°	276.5
10°	271.0
11°	264.8
12°	258.3
13°	251.4
14°	244.1
15°	236.5
17.5°	217.2
20°	197.9
22.5°	179.3
25°	161.7
27.5°	144.5
30°	128.3
32.5°	111.7
35°	95.2
37.5°	79.0
40°	63.8
42.5°	50.3
45°	38.6
47.5°	28.6
50°	20.0
52.5°	14.1
55°	11.7
57.5°	10.7
60°	9.7
62.5°	8.6
65°	7.6
67.5°	6.6
70°	5.5
72.5°	4.5
75°	3.8
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1271269

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)