

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270581

Luminaire Tested: P3AS20R359740D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359740D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 521.0 lumens
Efficiency: N/A
Efficacy: 18.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270581

CATALOG NUMBER: P3AS20R359740D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270581

CATALOG NUMBER: P3AS20R359740D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167465
5°	163328
10°	149318
15°	126743
20°	100342
25°	75900
30°	55249
35°	37370
40°	22957
45°	13180
50°	7949
55°	6423
60°	5614
65°	4981
70°	4103
75°	4067
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13180 cd/sqm

TEST NUMBER: P1270581

CATALOG NUMBER: P3AS20R359740D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	13.2
10°-20°	153.9	29.5
20°-30°	144.0	27.6
30°-40°	88.1	16.9
40°-50°	34.8	6.7
50°-60°	15.3	2.9
60°-70°	9.5	1.8
70°-80°	5.1	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.5	70.3
0°-40°	454.6	87.3
0°-60°	504.7	96.9
0°-90°	521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	764	
5°	742	69
15°	558	154
25°	314	144
35°	140	88
45°	42	35
55°	17	15
65°	10	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1270581

CATALOG NUMBER: P3AS20R359740D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	763.7
1°	764.5
2°	762.1
3°	757.3
4°	750.1
5°	742.0
6°	731.6
7°	719.6
8°	705.1
9°	689.1
10°	670.6
11°	651.4
12°	630.5
13°	608.1
14°	583.2
15°	558.3
17.5°	494.2
20°	430.0
22.5°	368.2
25°	313.7
27.5°	263.1
30°	218.2
32.5°	176.5
35°	139.6
37.5°	106.7
40°	80.2
42.5°	57.8
45°	42.5
47.5°	30.5
50°	23.3
52.5°	19.3
55°	16.8
57.5°	14.4
60°	12.8
62.5°	11.2
65°	9.6
67.5°	8.0
70°	6.4
72.5°	5.6
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8



TEST NUMBER: P1270581

CATALOG NUMBER: P3AS20R359740D010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)