

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271303

Luminaire Tested: P3AS05R359827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 224.0 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271303

CATALOG NUMBER: P3AS05R359827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271303

CATALOG NUMBER: P3AS05R359827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71990
5°	70218
10°	64194
15°	54507
20°	43147
25°	32639
30°	23750
35°	16062
40°	9876
45°	5675
50°	3411
55°	2753
60°	2412
65°	2127
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5675 cd/sqm

TEST NUMBER: P1271303

CATALOG NUMBER: P3AS05R359827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	13.2
10°-20°	66.2	29.6
20°-30°	61.9	27.6
30°-40°	37.9	16.9
40°-50°	14.9	6.7
50°-60°	6.6	2.9
60°-70°	4.1	1.8
70°-80°	2.2	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.6	70.4
0°-40°	195.5	87.3
0°-60°	217.0	96.9
0°-90°	224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	328	
5°	319	29
15°	240	66
25°	135	62
35°	60	38
45°	18	15
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1271303

CATALOG NUMBER: P3AS05R359827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	328.3
1°	328.7
2°	327.7
3°	325.6
4°	322.5
5°	319.0
6°	314.5
7°	309.4
8°	303.2
9°	296.3
10°	288.3
11°	280.1
12°	271.1
13°	261.4
14°	250.7
15°	240.1
17.5°	212.5
20°	184.9
22.5°	158.3
25°	134.9
27.5°	113.1
30°	93.8
32.5°	75.9
35°	60.0
37.5°	45.9
40°	34.5
42.5°	24.8
45°	18.3
47.5°	13.1
50°	10.0
52.5°	8.3
55°	7.2
57.5°	6.2
60°	5.5
62.5°	4.8
65°	4.1
67.5°	3.4
70°	2.8
72.5°	2.4
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3



TEST NUMBER: P1271303

CATALOG NUMBER: P3AS05R359827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)