

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270626

Luminaire Tested: P3AS20R459740D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459740D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 896.9 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270626

CATALOG NUMBER: P3AS20R459740D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270626

CATALOG NUMBER: P3AS20R459740D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336859
5°	328967
10°	302399
15°	256233
20°	198794
25°	138976
30°	87532
35°	51531
40°	29169
45°	14172
50°	4912
55°	3976
60°	3859
65°	3736
70°	3590
75°	3389
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14172 cd/sqm

TEST NUMBER: P1270626

CATALOG NUMBER: P3AS20R459740D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	15.4
10°-20°	309.9	34.6
20°-30°	263.2	29.3
30°-40°	125.5	14.0
40°-50°	37.8	4.2
50°-60°	9.6	1.1
60°-70°	7.1	0.8
70°-80°	4.2	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.5	79.3
0°-40°	837.0	93.3
0°-60°	884.4	98.6
0°-90°	896.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1536	
5°	1494	138
15°	1129	310
25°	574	263
35°	192	126
45°	46	38
55°	10	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1270626

CATALOG NUMBER: P3AS20R459740D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1536.2
2.5°	1526.6
5°	1494.5
7.5°	1439.1
10°	1358.1
12.5°	1250.6
15°	1128.7
17.5°	993.1
20°	851.9
22.5°	708.3
25°	574.4
27.5°	452.4
30°	345.7
32.5°	259.9
35°	192.5
37.5°	142.0
40°	101.9
42.5°	70.6
45°	45.7
47.5°	25.7
50°	14.4
52.5°	11.2
55°	10.4
57.5°	9.6
60°	8.8
62.5°	8.0
65°	7.2
67.5°	6.4
70°	5.6
72.5°	4.8
75°	4.0
77.5°	3.2
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)