

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271334

Luminaire Tested: P3AS05R409827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 402.0 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271334
CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1271334
 CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177880
5°	172705
10°	156733
15°	129490
20°	93411
25°	57778
30°	31271
35°	16169
40°	8788
45°	4931
50°	2456
55°	1835
60°	1667
65°	1608
70°	1539
75°	1440
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4931 cd/sqm



TEST NUMBER: P1271334
 CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	18.0
10°-20°	155.3	38.6
20°-30°	110.8	27.6
30°-40°	40.8	10.2
40°-50°	12.9	3.2
50°-60°	4.5	1.1
60°-70°	3.1	0.8
70°-80°	1.8	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.5	84.2
0°-40°	379.3	94.3
0°-60°	396.6	98.7
0°-90°	402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	402.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	811	
5°	785	72
15°	570	155
25°	239	111
35°	60	41
45°	16	13
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1271334
CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	811.2
2.5°	805.0
5°	784.6
7.5°	750.8
10°	703.9
12.5°	644.2
15°	570.4
17.5°	487.6
20°	400.3
22.5°	314.3
25°	238.8
27.5°	175.3
30°	123.5
32.5°	86.6
35°	60.4
37.5°	42.8
40°	30.7
42.5°	22.1
45°	15.9
47.5°	10.7
50°	7.2
52.5°	5.2
55°	4.8
57.5°	4.5
60°	3.8
62.5°	3.5
65°	3.1
67.5°	2.8
70°	2.4
72.5°	2.1
75°	1.7
77.5°	1.4
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)