

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271384

Luminaire Tested: P3AS05R509827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 125.0 lumens
Efficiency: N/A
Efficacy: 17.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271384
CATALOG NUMBER: P3AS05R509827DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1271384
 CATALOG NUMBER: P3AS05R509827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36357
5°	35373
10°	32620
15°	28695
20°	24012
25°	19041
30°	13977
35°	9610
40°	6097
45°	3411
50°	1842
55°	1567
60°	1316
65°	1245
70°	1090
75°	1017
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3411 cd/sqm



TEST NUMBER: P1271384
 CATALOG NUMBER: P3AS05R509827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.9	11.9
10°-20°	35.0	28.0
20°-30°	35.8	28.6
30°-40°	22.7	18.2
40°-50°	9.0	7.2
50°-60°	3.7	2.9
60°-70°	2.3	1.9
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	85.7	68.5
0°-40°	108.4	86.7
0°-60°	121.1	96.9
0°-90°	125.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	125.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	166	
5°	161	15
15°	126	35
25°	79	36
35°	36	23
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1271384
CATALOG NUMBER: P3AS05R509827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	165.8
2.5°	164.6
5°	160.7
7.5°	154.6
10°	146.5
12.5°	136.9
15°	126.4
17.5°	114.9
20°	102.9
22.5°	90.8
25°	78.7
27.5°	66.5
30°	55.2
32.5°	45.0
35°	35.9
37.5°	28.1
40°	21.3
42.5°	15.7
45°	11.0
47.5°	7.4
50°	5.4
52.5°	4.6
55°	4.1
57.5°	3.6
60°	3.0
62.5°	2.7
65°	2.4
67.5°	2.0
70°	1.7
72.5°	1.4
75°	1.2
77.5°	0.8
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)