

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270670

Luminaire Tested: P3AS20R509740D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509740D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.1 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270670
CATALOG NUMBER: P3AS20R509740D010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1270670
 CATALOG NUMBER: P3AS20R509740D010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351638
5°	342174
10°	315514
15°	277482
20°	232164
25°	184099
30°	135059
35°	92862
40°	59025
45°	32996
50°	17876
55°	15025
60°	12938
65°	11882
70°	10515
75°	9743
80°	8208
85°	8303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32996 cd/sqm



TEST NUMBER: P1270670
 CATALOG NUMBER: P3AS20R509740D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.0	11.9
10°-20°	338.5	28.0
20°-30°	346.3	28.6
30°-40°	219.6	18.2
40°-50°	87.4	7.2
50°-60°	35.4	2.9
60°-70°	22.7	1.9
70°-80°	11.7	1.0
80°-90°	3.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.8	68.5
0°-40°	1048.4	86.7
0°-60°	1171.2	96.9
0°-90°	1209.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1604	
5°	1554	144
15°	1222	339
25°	761	346
35°	347	220
45°	106	87
55°	39	35
65°	23	23
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P1270670
CATALOG NUMBER: P3AS20R509740D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1603.6
2.5°	1592.1
5°	1554.5
7.5°	1495.6
10°	1417.0
12.5°	1323.8
15°	1222.3
17.5°	1111.1
20°	994.9
22.5°	878.7
25°	760.9
27.5°	643.1
30°	533.4
32.5°	435.3
35°	346.9
37.5°	271.6
40°	206.2
42.5°	152.2
45°	106.4
47.5°	72.0
50°	52.4
52.5°	44.2
55°	39.3
57.5°	34.4
60°	29.5
62.5°	26.2
65°	22.9
67.5°	19.6
70°	16.4
72.5°	13.1
75°	11.5
77.5°	8.2
80°	6.5
82.5°	4.9
85°	3.3
87.5°	1.6
90°	0.0

(END OF REPORT)