

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270719

Luminaire Tested: P3AS20R609740D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609740D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 662.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270719

CATALOG NUMBER: P3AS20R609740D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270719

CATALOG NUMBER: P3AS20R609740D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117513
5°	116200
10°	112178
15°	105971
20°	97682
25°	88457
30°	78518
35°	67110
40°	53357
45°	37616
50°	22481
55°	11354
60°	10920
65°	10014
70°	9296
75°	8811
80°	8082
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37616 cd/sqm

TEST NUMBER: P1270719

CATALOG NUMBER: P3AS20R609740D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	7.5
10°-20°	130.5	19.7
20°-30°	167.5	25.3
30°-40°	155.3	23.5
40°-50°	94.6	14.3
50°-60°	31.5	4.8
60°-70°	19.2	2.9
70°-80°	10.8	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.6	52.5
0°-40°	502.9	76.0
0°-60°	629.0	95.0
0°-90°	662.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	662.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	536	
5°	528	50
15°	467	130
25°	366	168
35°	251	155
45°	121	95
55°	30	32
65°	19	19
75°	10	11
85°	2	3
90°	0	

TEST NUMBER: P1270719

CATALOG NUMBER: P3AS20R609740D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	535.9
2.5°	533.5
5°	527.9
7.5°	517.4
10°	503.8
12.5°	486.9
15°	466.8
17.5°	443.5
20°	418.6
22.5°	392.1
25°	365.6
27.5°	338.3
30°	310.1
32.5°	282.0
35°	250.7
37.5°	217.7
40°	186.4
42.5°	153.5
45°	121.3
47.5°	94.0
50°	65.9
52.5°	39.4
55°	29.7
57.5°	27.3
60°	24.9
62.5°	21.7
65°	19.3
67.5°	16.9
70°	14.5
72.5°	12.1
75°	10.4
77.5°	8.0
80°	6.4
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

(END OF REPORT)