

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270730

Luminaire Tested: P3AS20R609740D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609740D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1191.0 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270730

CATALOG NUMBER: P3AS20R609740D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270730

CATALOG NUMBER: P3AS20R609740D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	301840
5°	295069
10°	276236
15°	247833
20°	213122
25°	176212
30°	139237
35°	103410
40°	71219
45°	44656
50°	24562
55°	14375
60°	12938
65°	11052
70°	9425
75°	9743
80°	8208
85°	8303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44656 cd/sqm

TEST NUMBER: P1270730

CATALOG NUMBER: P3AS20R609740D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	10.5
10°-20°	303.2	25.5
20°-30°	332.6	27.9
30°-40°	242.3	20.3
40°-50°	114.4	9.6
50°-60°	37.5	3.1
60°-70°	21.3	1.8
70°-80°	11.4	1.0
80°-90°	3.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.5	63.9
0°-40°	1002.8	84.2
0°-60°	1154.8	97.0
0°-90°	1191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1376	
5°	1340	125
15°	1092	303
25°	728	333
35°	386	242
45°	144	114
55°	38	37
65°	21	21
75°	12	11
85°	3	4
90°	0	

TEST NUMBER: P1270730

CATALOG NUMBER: P3AS20R609740D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1376.5
2.5°	1368.3
5°	1340.5
7.5°	1297.9
10°	1240.6
12.5°	1171.9
15°	1091.7
17.5°	1004.9
20°	913.3
22.5°	820.0
25°	728.3
27.5°	636.7
30°	549.9
32.5°	466.5
35°	386.3
37.5°	314.3
40°	248.8
42.5°	191.5
45°	144.0
47.5°	104.8
50°	72.0
52.5°	47.5
55°	37.6
57.5°	32.7
60°	29.5
62.5°	24.6
65°	21.3
67.5°	18.0
70°	14.7
72.5°	13.1
75°	11.5
77.5°	8.2
80°	6.5
82.5°	4.9
85°	3.3
87.5°	1.6
90°	0.0

(END OF REPORT)