

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270731

Luminaire Tested: P3AS20R659740D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659740D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2025.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270731

CATALOG NUMBER: P3AS20R659740D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1270731

CATALOG NUMBER: P3AS20R659740D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494873
5°	465748
10°	459845
15°	451717
20°	426500
25°	395854
30°	307693
35°	177989
40°	71734
45°	33027
50°	12861
55°	5008
60°	4298
65°	4255
70°	4231
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33027 cd/sqm

TEST NUMBER: P1270731

CATALOG NUMBER: P3AS20R659740D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.1	9.9
10°-20°	555.7	27.4
20°-30°	727.4	35.9
30°-40°	421.3	20.8
40°-50°	90.2	4.5
50°-60°	14.7	0.7
60°-70°	8.1	0.4
70°-80°	4.8	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1484.2	73.3
0°-40°	1905.5	94.1
0°-60°	2010.4	99.3
0°-90°	2025.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2025.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2257	
5°	2116	201
15°	1990	556
25°	1636	727
35°	665	421
45°	106	90
55°	13	15
65°	8	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1270731

CATALOG NUMBER: P3AS20R659740D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2256.8
2.5°	2192.9
5°	2115.9
7.5°	2084.8
10°	2065.2
12.5°	2037.3
15°	1989.8
17.5°	1916.1
20°	1827.7
22.5°	1744.2
25°	1636.1
27.5°	1454.3
30°	1215.2
32.5°	941.7
35°	664.9
37.5°	420.9
40°	250.6
42.5°	157.2
45°	106.5
47.5°	68.8
50°	37.7
52.5°	18.0
55°	13.1
57.5°	11.5
60°	9.8
62.5°	9.8
65°	8.2
67.5°	6.6
70°	6.6
72.5°	4.9
75°	4.9
77.5°	3.3
80°	3.3
82.5°	1.6
85°	1.6
87.5°	1.6
90°	0.0

(END OF REPORT)