

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271432

Luminaire Tested: P3AS05R609827DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609827DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 363.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271432

CATALOG NUMBER: P3AS05R609827DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1271432

CATALOG NUMBER: P3AS05R609827DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85717
5°	84900
10°	82430
15°	77231
20°	68349
25°	57173
30°	44817
35°	32498
40°	21641
45°	13490
50°	7300
55°	2103
60°	1974
65°	1816
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13490 cd/sqm

TEST NUMBER: P1271432

CATALOG NUMBER: P3AS05R609827DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	10.0
10°-20°	94.4	26.0
20°-30°	107.6	29.6
30°-40°	76.3	21.0
40°-50°	34.6	9.5
50°-60°	7.3	2.0
60°-70°	3.5	1.0
70°-80°	2.2	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.3	65.6
0°-40°	314.6	86.7
0°-60°	356.5	98.2
0°-90°	363.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	363.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	391	
5°	386	36
15°	340	94
25°	236	108
35°	121	76
45°	44	35
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1271432

CATALOG NUMBER: P3AS05R609827DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	390.9
2.5°	389.5
5°	385.7
7.5°	379.2
10°	370.2
12.5°	357.4
15°	340.2
17.5°	318.4
20°	292.9
22.5°	265.3
25°	236.3
27.5°	206.7
30°	177.0
32.5°	148.7
35°	121.4
37.5°	97.3
40°	75.6
42.5°	57.3
45°	43.5
47.5°	32.4
50°	21.4
52.5°	10.0
55°	5.5
57.5°	4.8
60°	4.5
62.5°	4.1
65°	3.5
67.5°	3.1
70°	2.8
72.5°	2.4
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)