

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270748

Luminaire Tested: P3AS20R659740D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659740D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 632.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270748

CATALOG NUMBER: P3AS20R659740D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270748

CATALOG NUMBER: P3AS20R659740D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112469
5°	110962
10°	107235
15°	101136
20°	93271
25°	84682
30°	74999
35°	63818
40°	50781
45°	35849
50°	20810
55°	11354
60°	10569
65°	9599
70°	8719
75°	8133
80°	7072
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35849 cd/sqm

TEST NUMBER: P1270748

CATALOG NUMBER: P3AS20R659740D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	7.5
10°-20°	124.6	19.7
20°-30°	160.2	25.3
30°-40°	148.2	23.4
40°-50°	89.5	14.2
50°-60°	30.5	4.8
60°-70°	18.4	2.9
70°-80°	10.3	1.6
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.2	52.6
0°-40°	480.4	76.0
0°-60°	600.3	95.0
0°-90°	632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	632.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	513	
5°	504	47
15°	446	125
25°	350	160
35°	238	148
45°	116	89
55°	30	31
65°	18	18
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1270748

CATALOG NUMBER: P3AS20R659740D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	512.9
2.5°	510.5
5°	504.1
7.5°	494.4
10°	481.6
12.5°	465.5
15°	445.5
17.5°	423.8
20°	399.7
22.5°	374.8
25°	350.0
27.5°	323.5
30°	296.2
32.5°	268.9
35°	238.4
37.5°	208.7
40°	177.4
42.5°	146.1
45°	115.6
47.5°	87.5
50°	61.0
52.5°	38.5
55°	29.7
57.5°	26.5
60°	24.1
62.5°	20.9
65°	18.5
67.5°	16.1
70°	13.6
72.5°	12.0
75°	9.6
77.5°	8.0
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

(END OF REPORT)