

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270754

Luminaire Tested: P3AS20R659740D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659740D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 555.9 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270754

CATALOG NUMBER: P3AS20R659740D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270754

CATALOG NUMBER: P3AS20R659740D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141326
5°	137816
10°	128343
15°	115006
20°	99339
25°	82626
30°	65149
35°	48292
40°	33262
45°	20622
50°	11224
55°	7034
60°	5964
65°	5396
70°	4616
75°	4067
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20622 cd/sqm

TEST NUMBER: P1270754

CATALOG NUMBER: P3AS20R659740D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.2	10.5
10°-20°	140.8	25.3
20°-30°	155.7	28.0
30°-40°	113.1	20.3
40°-50°	53.0	9.5
50°-60°	17.8	3.2
60°-70°	10.3	1.8
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.7	63.8
0°-40°	467.7	84.1
0°-60°	538.5	96.9
0°-90°	555.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	555.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	626	58
15°	507	141
25°	342	156
35°	180	113
45°	66	53
55°	18	18
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1270754

CATALOG NUMBER: P3AS20R659740D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	644.5
2.5°	640.5
5°	626.1
7.5°	604.4
10°	576.4
12.5°	543.5
15°	506.6
17.5°	466.5
20°	425.7
22.5°	383.2
25°	341.5
27.5°	299.0
30°	257.3
32.5°	217.2
35°	180.4
37.5°	146.7
40°	116.2
42.5°	89.0
45°	66.5
47.5°	48.1
50°	32.9
52.5°	22.4
55°	18.4
57.5°	16.0
60°	13.6
62.5°	12.0
65°	10.4
67.5°	8.8
70°	7.2
72.5°	6.4
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)