

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270815

Luminaire Tested: P3AS02R159827DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159827DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 211.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270815

CATALOG NUMBER: P3AS02R159827DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1270815

CATALOG NUMBER: P3AS02R159827DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	97	95
4	107	103	100	97		106	102	99	97		100	97	95		98	96	94		97	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	92
6	103	98	94	92		102	97	94	92		96	93	91		95	92	91		94	92	90
7	101	96	92	90		100	95	92	90		94	91	89		93	91	89		92	90	89
8	99	94	90	88		98	93	90	88		92	90	88		92	89	87		91	89	87
9	97	92	89	87		97	92	89	86		91	88	86		90	88	86		90	87	86
10	96	90	87	85		95	90	87	85		89	87	85		89	86	85		88	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410143
5°	343737
10°	161921
15°	48808
20°	18062
25°	7017
30°	2608
35°	803
40°	286
45°	155
50°	102
55°	115
60°	132
65°	104
70°	128
75°	169
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 169 cd/sqm

TEST NUMBER: P1270815

CATALOG NUMBER: P3AS02R159827DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	57.2
10°-20°	71.8	34.0
20°-30°	15.1	7.1
30°-40°	2.4	1.2
40°-50°	0.4	0.2
50°-60°	0.3	0.1
60°-70°	0.2	0.1
70°-80°	0.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.6	98.4
0°-40°	210.0	99.5
0°-60°	210.7	99.8
0°-90°	211.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	211.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1870	
5°	1562	121
15°	215	72
25°	29	15
35°	3	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270815

CATALOG NUMBER: P3AS02R159827DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1870.4
1°	1864.5
2°	1834.8
3°	1775.4
4°	1688.4
5°	1561.6
6°	1412.6
7°	1242.3
8°	1079.6
9°	895.5
10°	727.2
12.5°	392.4
15°	215.0
17.5°	125.9
20°	77.4
22.5°	47.4
25°	29.0
27.5°	17.5
30°	10.3
32.5°	5.8
35°	3.0
37.5°	1.7
40°	1.0
42.5°	0.7
45°	0.5
47.5°	0.3
50°	0.3
52.5°	0.3
55°	0.3
57.5°	0.3
60°	0.3
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)