

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271615

Luminaire Tested: P3AS09R309827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 160.9 lumens
Efficiency: N/A
Efficacy: 14.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271615

CATALOG NUMBER: P3AS09R309827DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271615

CATALOG NUMBER: P3AS09R309827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55018
5°	53313
10°	48029
15°	39728
20°	30756
25°	23082
30°	16762
35°	11163
40°	6870
45°	4031
50°	2456
55°	1988
60°	1754
65°	1401
70°	1282
75°	1271
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4031 cd/sqm

TEST NUMBER: P1271615

CATALOG NUMBER: P3AS09R309827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.3	13.8
10°-20°	48.2	30.0
20°-30°	43.9	27.3
30°-40°	26.5	16.5
40°-50°	10.6	6.6
50°-60°	4.7	2.9
60°-70°	2.8	1.8
70°-80°	1.5	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.3	71.0
0°-40°	140.8	87.5
0°-60°	156.2	97.0
0°-90°	160.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	160.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	251	
5°	242	22
15°	175	48
25°	95	44
35°	42	27
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1271615

CATALOG NUMBER: P3AS09R309827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	250.9
1°	250.6
2°	249.6
3°	247.9
4°	245.4
5°	242.2
6°	238.2
7°	233.9
8°	228.4
9°	222.2
10°	215.7
11°	208.2
12°	200.2
13°	192.2
14°	183.5
15°	175.0
17.5°	152.8
20°	131.8
22.5°	112.3
25°	95.4
27.5°	79.9
30°	66.2
32.5°	53.4
35°	41.7
37.5°	32.0
40°	24.0
42.5°	17.5
45°	13.0
47.5°	9.7
50°	7.2
52.5°	5.7
55°	5.2
57.5°	4.5
60°	4.0
62.5°	3.2
65°	2.7
67.5°	2.5
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1271615
CATALOG NUMBER: P3AS09R309827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)