

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271617

Luminaire Tested: P3AS09R309827DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271617  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R309827DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 328.0 lumens  
Efficiency: N/A  
Efficacy: 29.8 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271617  
CATALOG NUMBER: P3AS09R309827DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1271617  
 CATALOG NUMBER: P3AS09R309827DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80				80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70				70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61				61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55				55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52				52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	112074
5°	108584
10°	97838
15°	80931
20°	62655
25°	47011
30°	34132
35°	22727
40°	13969
45°	8187
50°	5015
55°	4091
60°	3552
65°	2906
70°	2629
75°	2626
80°	1894
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8187 cd/sqm



TEST NUMBER: P1271617  
 CATALOG NUMBER: P3AS09R309827DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	13.8
10°-20°	98.2	29.9
20°-30°	89.3	27.2
30°-40°	54.0	16.5
40°-50°	21.6	6.6
50°-60°	9.6	2.9
60°-70°	5.8	1.8
70°-80°	3.2	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.9	71.0
0°-40°	286.9	87.5
0°-60°	318.1	97.0
0°-90°	328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	328.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	511	
5°	493	45
15°	356	98
25°	194	89
35°	85	54
45°	26	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1271617  
CATALOG NUMBER: P3AS09R309827DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	511.1
1°	510.6
2°	508.6
3°	505.0
4°	500.0
5°	493.3
6°	485.2
7°	476.6
8°	465.4
9°	452.7
10°	439.4
11°	424.2
12°	407.9
13°	391.6
14°	373.8
15°	356.5
17.5°	311.3
20°	268.5
22.5°	228.9
25°	194.3
27.5°	162.8
30°	134.8
32.5°	108.8
35°	84.9
37.5°	65.1
40°	48.8
42.5°	35.6
45°	26.4
47.5°	19.8
50°	14.7
52.5°	11.7
55°	10.7
57.5°	9.2
60°	8.1
62.5°	6.6
65°	5.6
67.5°	5.1
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.5
80°	1.5
82.5°	1.0
85°	1.0
87.5°	0.5



TEST NUMBER: P1271617  
CATALOG NUMBER: P3AS09R309827DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)