

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270916

Luminaire Tested: P3AS02R309827DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309827DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 176.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270916

CATALOG NUMBER: P3AS02R309827DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1270916

CATALOG NUMBER: P3AS02R309827DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102711
5°	97755
10°	82230
15°	59297
20°	36777
25°	20929
30°	11622
35°	6318
40°	3321
45°	1799
50°	955
55°	650
60°	570
65°	623
70°	513
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1799 cd/sqm

TEST NUMBER: P1270916

CATALOG NUMBER: P3AS02R309827DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	22.7
10°-20°	71.1	40.4
20°-30°	41.1	23.3
30°-40°	15.6	8.9
40°-50°	4.8	2.7
50°-60°	1.6	0.9
60°-70°	1.1	0.6
70°-80°	0.6	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	152.1	86.4
0°-40°	167.7	95.3
0°-60°	174.1	98.9
0°-90°	176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	176.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	468	
5°	444	40
15°	261	71
25°	86	41
35°	24	16
45°	6	5
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1270916

CATALOG NUMBER: P3AS02R309827DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	468.4
1°	468.0
2°	465.2
3°	459.9
4°	453.2
5°	444.1
6°	432.4
7°	419.5
8°	405.0
9°	387.7
10°	369.3
11°	349.3
12°	328.2
13°	306.1
14°	283.6
15°	261.2
17.5°	206.0
20°	157.6
22.5°	116.9
25°	86.5
27.5°	62.8
30°	45.9
32.5°	33.1
35°	23.6
37.5°	16.5
40°	11.6
42.5°	8.1
45°	5.8
47.5°	4.0
50°	2.8
52.5°	2.0
55°	1.7
57.5°	1.5
60°	1.3
62.5°	1.2
65°	1.2
67.5°	1.0
70°	0.8
72.5°	0.7
75°	0.5
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.0



TEST NUMBER: P1270916

CATALOG NUMBER: P3AS02R309827DE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)