

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271646

Luminaire Tested: P3AS09R359827DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359827DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271646

CATALOG NUMBER: P3AS09R359827DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271646

CATALOG NUMBER: P3AS09R359827DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106066
5°	103456
10°	94587
15°	80273
20°	63542
25°	48075
30°	34993
35°	23664
40°	14542
45°	8342
50°	5015
55°	4091
60°	3552
65°	3165
70°	2629
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8342 cd/sqm

TEST NUMBER: P1271646

CATALOG NUMBER: P3AS09R359827DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	13.2
10°-20°	97.5	29.5
20°-30°	91.2	27.6
30°-40°	55.8	16.9
40°-50°	22.0	6.7
50°-60°	9.7	2.9
60°-70°	6.0	1.8
70°-80°	3.2	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.1	70.4
0°-40°	288.0	87.3
0°-60°	319.6	96.9
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	470	43
15°	354	97
25°	199	91
35°	88	56
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1271646

CATALOG NUMBER: P3AS09R359827DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	483.7
1°	484.2
2°	482.7
3°	479.7
4°	475.1
5°	470.0
6°	463.4
7°	455.8
8°	446.6
9°	436.5
10°	424.8
11°	412.6
12°	399.4
13°	385.1
14°	369.4
15°	353.6
17.5°	313.0
20°	272.3
22.5°	233.2
25°	198.7
27.5°	166.7
30°	138.2
32.5°	111.8
35°	88.4
37.5°	67.6
40°	50.8
42.5°	36.6
45°	26.9
47.5°	19.3
50°	14.7
52.5°	12.2
55°	10.7
57.5°	9.1
60°	8.1
62.5°	7.1
65°	6.1
67.5°	5.1
70°	4.1
72.5°	3.6
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5



TEST NUMBER: P1271646
CATALOG NUMBER: P3AS09R359827DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)