

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271647

Luminaire Tested: P3AS09R359827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 535.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271647
CATALOG NUMBER: P3AS09R359827DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1271647
 CATALOG NUMBER: P3AS09R359827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269825
5°	259321
10°	225959
15°	173054
20°	115790
25°	70069
30°	40209
35°	22486
40°	11937
45°	6140
50°	2968
55°	2332
60°	2237
65°	1868
70°	1988
75°	1694
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6140 cd/sqm



TEST NUMBER: P1271647
 CATALOG NUMBER: P3AS09R359827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	20.0
10°-20°	207.7	38.8
20°-30°	136.0	25.4
30°-40°	55.2	10.3
40°-50°	16.5	3.1
50°-60°	5.6	1.1
60°-70°	3.8	0.7
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.9	84.3
0°-40°	506.1	94.6
0°-60°	528.2	98.7
0°-90°	535.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	535.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1230	
5°	1178	107
15°	762	208
25°	290	136
35°	84	55
45°	20	17
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1271647
CATALOG NUMBER: P3AS09R359827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1230.5
1°	1228.5
2°	1222.9
3°	1211.7
4°	1198.5
5°	1178.1
6°	1152.7
7°	1124.2
8°	1092.1
9°	1055.5
10°	1014.8
11°	969.5
12°	922.1
13°	869.2
14°	818.8
15°	762.3
17.5°	625.4
20°	496.2
22.5°	381.7
25°	289.6
27.5°	215.8
30°	158.8
32.5°	116.5
35°	84.0
37.5°	59.5
40°	41.7
42.5°	29.0
45°	19.8
47.5°	13.2
50°	8.7
52.5°	6.6
55°	6.1
57.5°	5.6
60°	5.1
62.5°	4.6
65°	3.6
67.5°	3.1
70°	3.1
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1271647
CATALOG NUMBER: P3AS09R359827DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)