

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270920

Luminaire Tested: P3AS02R309827DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309827DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 136.1 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270920

CATALOG NUMBER: P3AS02R309827DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1270920

CATALOG NUMBER: P3AS02R309827DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	49	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32125
5°	31411
10°	29213
15°	25993
20°	22355
25°	18945
30°	15724
35°	12341
40°	8845
45°	5799
50°	3309
55°	2179
60°	2061
65°	1920
70°	1731
75°	1525
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5799 cd/sqm

TEST NUMBER: P1270920

CATALOG NUMBER: P3AS02R309827DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.2	9.7
10°-20°	31.8	23.4
20°-30°	35.9	26.4
30°-40°	28.7	21.1
40°-50°	14.7	10.8
50°-60°	5.5	4.1
60°-70°	3.7	2.7
70°-80°	2.0	1.4
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.9	59.5
0°-40°	109.6	80.5
0°-60°	129.9	95.4
0°-90°	136.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	136.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	146	
5°	143	13
15°	114	32
25°	78	36
35°	46	29
45°	19	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1270920

CATALOG NUMBER: P3AS02R309827DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	146.5
1°	146.5
2°	146.0
3°	145.2
4°	144.0
5°	142.7
6°	141.0
7°	138.8
8°	136.5
9°	133.8
10°	131.2
11°	128.2
12°	125.0
13°	121.7
14°	118.2
15°	114.5
17.5°	105.1
20°	95.8
22.5°	86.8
25°	78.3
27.5°	69.9
30°	62.1
32.5°	54.1
35°	46.1
37.5°	38.2
40°	30.9
42.5°	24.4
45°	18.7
47.5°	13.9
50°	9.7
52.5°	6.8
55°	5.7
57.5°	5.2
60°	4.7
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.7
72.5°	2.2
75°	1.8
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.5
87.5°	0.2



TEST NUMBER: P1270920

CATALOG NUMBER: P3AS02R309827DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):



(END OF REPORT)