

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271672

Luminaire Tested: P3AS09R409827DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409827DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 455.0 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271672
CATALOG NUMBER: P3AS09R409827DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271672
 CATALOG NUMBER: P3AS09R409827DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102141
5°	100286
10°	94543
15°	85857
20°	75443
25°	64407
30°	53350
35°	41144
40°	29283
45°	19723
50°	10780
55°	7608
60°	7149
65°	6590
70°	5898
75°	5592
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19723 cd/sqm



TEST NUMBER: P1271672
 CATALOG NUMBER: P3AS09R409827DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	9.3
10°-20°	105.4	23.2
20°-30°	121.8	26.8
30°-40°	96.0	21.1
40°-50°	49.3	10.8
50°-60°	18.8	4.1
60°-70°	12.5	2.7
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.6	59.3
0°-40°	365.6	80.4
0°-60°	433.7	95.3
0°-90°	455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	455.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	456	42
15°	378	105
25°	266	122
35°	154	96
45°	64	49
55°	20	19
65°	13	12
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1271672
CATALOG NUMBER: P3AS09R409827DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	465.8
2.5°	463.2
5°	455.6
7.5°	442.4
10°	424.6
12.5°	403.7
15°	378.2
17.5°	351.8
20°	323.3
22.5°	294.2
25°	266.2
27.5°	238.2
30°	210.7
32.5°	182.8
35°	153.7
37.5°	126.8
40°	102.3
42.5°	81.4
45°	63.6
47.5°	46.3
50°	31.6
52.5°	22.9
55°	19.9
57.5°	17.8
60°	16.3
62.5°	14.3
65°	12.7
67.5°	10.7
70°	9.2
72.5°	7.6
75°	6.6
77.5°	5.1
80°	3.6
82.5°	3.1
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)