

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270958

Luminaire Tested: P3AS02R359827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 108.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270958

CATALOG NUMBER: P3AS02R359827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270958

CATALOG NUMBER: P3AS02R359827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	80	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34712
5°	33854
10°	30950
15°	26266
20°	20792
25°	15727
30°	11445
35°	7736
40°	4752
45°	2729
50°	1637
55°	1338
60°	1184
65°	1038
70°	833
75°	847
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2729 cd/sqm

TEST NUMBER: P1270958

CATALOG NUMBER: P3AS02R359827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.2	13.2
10°-20°	31.9	29.5
20°-30°	29.8	27.6
30°-40°	18.3	16.9
40°-50°	7.2	6.7
50°-60°	3.2	2.9
60°-70°	2.0	1.8
70°-80°	1.1	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	75.9	70.3
0°-40°	94.2	87.2
0°-60°	104.6	96.9
0°-90°	108.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	108.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	158	
5°	154	14
15°	116	32
25°	65	30
35°	29	18
45°	9	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1270958

CATALOG NUMBER: P3AS02R359827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	158.3
1°	158.5
2°	158.0
3°	157.0
4°	155.5
5°	153.8
6°	151.7
7°	149.2
8°	146.2
9°	142.8
10°	139.0
11°	135.0
12°	130.7
13°	126.0
14°	120.9
15°	115.7
17.5°	102.4
20°	89.1
22.5°	76.3
25°	65.0
27.5°	54.5
30°	45.2
32.5°	36.6
35°	28.9
37.5°	22.1
40°	16.6
42.5°	12.0
45°	8.8
47.5°	6.3
50°	4.8
52.5°	4.0
55°	3.5
57.5°	3.0
60°	2.7
62.5°	2.3
65°	2.0
67.5°	1.7
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2



TEST NUMBER: P1270958

CATALOG NUMBER: P3AS02R359827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)