

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270984

Luminaire Tested: P3AS02R409827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 149.0 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270984
CATALOG NUMBER: P3AS02R409827DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1270984

CATALOG NUMBER: P3AS02R409827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.9	9.3
10°-20°	34.5	23.2
20°-30°	39.9	26.8
30°-40°	31.4	21.1
40°-50°	16.1	10.8
50°-60°	6.2	4.1
60°-70°	4.1	2.7
70°-80°	2.2	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.3	59.3
0°-40°	119.7	80.4
0°-60°	142.0	95.3
0°-90°	149.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	149.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	152	
5°	149	14
15°	124	35
25°	87	40
35°	50	31
45°	21	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1270984

CATALOG NUMBER: P3AS02R409827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	152.5
2.5°	151.7
5°	149.2
7.5°	144.9
10°	139.0
12.5°	132.2
15°	123.9
17.5°	115.2
20°	105.9
22.5°	96.4
25°	87.2
27.5°	78.0
30°	69.0
32.5°	59.8
35°	50.3
37.5°	41.5
40°	33.5
42.5°	26.7
45°	20.8
47.5°	15.2
50°	10.3
52.5°	7.5
55°	6.5
57.5°	5.8
60°	5.3
62.5°	4.7
65°	4.2
67.5°	3.5
70°	3.0
72.5°	2.5
75°	2.2
77.5°	1.7
80°	1.2
82.5°	1.0
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)