

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271003

Luminaire Tested: P3AS02R459827DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459827DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271003

CATALOG NUMBER: P3AS02R459827DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271003

CATALOG NUMBER: P3AS02R459827DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69841
5°	68215
10°	62702
15°	53122
20°	41234
25°	28816
30°	18155
35°	10681
40°	6040
45°	2946
50°	1023
55°	841
60°	789
65°	778
70°	769
75°	678
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2946 cd/sqm

TEST NUMBER: P1271003

CATALOG NUMBER: P3AS02R459827DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.7	15.4
10°-20°	64.3	34.6
20°-30°	54.6	29.3
30°-40°	26.0	14.0
40°-50°	7.8	4.2
50°-60°	2.0	1.1
60°-70°	1.5	0.8
70°-80°	0.9	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	147.5	79.3
0°-40°	173.6	93.3
0°-60°	183.4	98.6
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	318	
5°	310	29
15°	234	64
25°	119	55
35°	40	26
45°	10	8
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271003

CATALOG NUMBER: P3AS02R459827DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	318.5
2.5°	316.5
5°	309.9
7.5°	298.4
10°	281.6
12.5°	259.3
15°	234.0
17.5°	205.9
20°	176.7
22.5°	146.9
25°	119.1
27.5°	93.8
30°	71.7
32.5°	53.9
35°	39.9
37.5°	29.4
40°	21.1
42.5°	14.6
45°	9.5
47.5°	5.3
50°	3.0
52.5°	2.3
55°	2.2
57.5°	2.0
60°	1.8
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.2
72.5°	1.0
75°	0.8
77.5°	0.7
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)