

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271027

Luminaire Tested: P3AS02R509827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 92.0 lumens
Efficiency: N/A
Efficacy: 25.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271027

CATALOG NUMBER: P3AS02R509827DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271027

CATALOG NUMBER: P3AS02R509827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29296
5°	28703
10°	26875
15°	24064
20°	20255
25°	15461
30°	10052
35°	5943
40°	3435
45°	1737
50°	648
55°	497
60°	482
65°	415
70°	449
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1737 cd/sqm

TEST NUMBER: P1271027

CATALOG NUMBER: P3AS02R509827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.1	13.2
10°-20°	29.3	31.9
20°-30°	28.8	31.3
30°-40°	14.5	15.7
40°-50°	4.6	5.0
50°-60°	1.2	1.3
60°-70°	0.8	0.9
70°-80°	0.5	0.6
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	70.2	76.3
0°-40°	84.7	92.1
0°-60°	90.5	98.3
0°-90°	92.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	92.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	134	
5°	130	12
15°	106	29
25°	64	29
35°	22	14
45°	6	5
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1271027

CATALOG NUMBER: P3AS02R509827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	133.6
2.5°	132.8
5°	130.4
7.5°	126.1
10°	120.7
12.5°	113.8
15°	106.0
17.5°	97.0
20°	86.8
22.5°	75.7
25°	63.9
27.5°	51.3
30°	39.7
32.5°	29.9
35°	22.2
37.5°	16.4
40°	12.0
42.5°	8.5
45°	5.6
47.5°	3.2
50°	1.9
52.5°	1.4
55°	1.3
57.5°	1.1
60°	1.1
62.5°	1.0
65°	0.8
67.5°	0.7
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)