

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271792

Luminaire Tested: P3AS09R609827DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R609827DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 370.0 lumens  
Efficiency: N/A  
Efficacy: 33.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271792  
CATALOG NUMBER: P3AS09R609827DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1271792

CATALOG NUMBER: P3AS09R609827DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93764
5°	91657
10°	85814
15°	76981
20°	66202
25°	54753
30°	43247
35°	32123
40°	22127
45°	13862
50°	7642
55°	4473
60°	4035
65°	3424
70°	2949
75°	3050
80°	2526
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13862 cd/sqm



TEST NUMBER: P1271792  
 CATALOG NUMBER: P3AS09R609827DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.8	10.5
10°-20°	94.2	25.5
20°-30°	103.3	27.9
30°-40°	75.3	20.3
40°-50°	35.5	9.6
50°-60°	11.7	3.1
60°-70°	6.6	1.8
70°-80°	3.6	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.3	63.9
0°-40°	311.5	84.2
0°-60°	358.7	97.0
0°-90°	370.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	370.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	428	
5°	416	39
15°	339	94
25°	226	103
35°	120	75
45°	45	36
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1271792  
CATALOG NUMBER: P3AS09R609827DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	427.6
2.5°	425.1
5°	416.4
7.5°	403.2
10°	385.4
12.5°	364.1
15°	339.1
17.5°	312.2
20°	283.7
22.5°	254.7
25°	226.3
27.5°	197.8
30°	170.8
32.5°	144.9
35°	120.0
37.5°	97.6
40°	77.3
42.5°	59.5
45°	44.7
47.5°	32.5
50°	22.4
52.5°	14.7
55°	11.7
57.5°	10.2
60°	9.2
62.5°	7.6
65°	6.6
67.5°	5.6
70°	4.6
72.5°	4.1
75°	3.6
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)