

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271044

Luminaire Tested: P3AS02R509827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 123.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271044

CATALOG NUMBER: P3AS02R509827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271044

CATALOG NUMBER: P3AS02R509827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35765
5°	34801
10°	32108
15°	28241
20°	23615
25°	18727
30°	13749
35°	9450
40°	6011
45°	3349
50°	1808
55°	1529
60°	1316
65°	1193
70°	1090
75°	1017
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3349 cd/sqm

TEST NUMBER: P1271044

CATALOG NUMBER: P3AS02R509827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.7	11.9
10°-20°	34.4	28.0
20°-30°	35.2	28.6
30°-40°	22.3	18.2
40°-50°	8.9	7.2
50°-60°	3.6	2.9
60°-70°	2.3	1.9
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	84.3	68.5
0°-40°	106.7	86.7
0°-60°	119.1	96.9
0°-90°	123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	123.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	163	
5°	158	15
15°	124	34
25°	77	35
35°	35	22
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271044

CATALOG NUMBER: P3AS02R509827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	163.1
2.5°	162.0
5°	158.1
7.5°	152.2
10°	144.2
12.5°	134.7
15°	124.4
17.5°	113.0
20°	101.2
22.5°	89.4
25°	77.4
27.5°	65.4
30°	54.3
32.5°	44.3
35°	35.3
37.5°	27.6
40°	21.0
42.5°	15.5
45°	10.8
47.5°	7.3
50°	5.3
52.5°	4.5
55°	4.0
57.5°	3.5
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.3
75°	1.2
77.5°	0.8
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)