

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271067

Luminaire Tested: P3AS02R559827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 141.0 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271067

CATALOG NUMBER: P3AS02R559827DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271067

CATALOG NUMBER: P3AS02R559827DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26511
5°	26172
10°	25139
15°	23519
20°	21445
25°	19138
30°	16737
35°	13920
40°	10963
45°	7443
50°	4537
55°	2370
60°	2193
65°	2075
70°	1923
75°	1694
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7443 cd/sqm

TEST NUMBER: P1271067

CATALOG NUMBER: P3AS02R559827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	7.9
10°-20°	28.9	20.5
20°-30°	36.3	25.7
30°-40°	32.4	23.0
40°-50°	18.9	13.4
50°-60°	6.6	4.7
60°-70°	4.0	2.8
70°-80°	2.2	1.6
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	76.3	54.2
0°-40°	108.7	77.1
0°-60°	134.2	95.2
0°-90°	141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	141.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	121	
5°	119	11
15°	104	29
25°	79	36
35°	52	32
45°	24	19
55°	6	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1271067

CATALOG NUMBER: P3AS02R559827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	120.9
2.5°	120.2
5°	118.9
7.5°	116.2
10°	112.9
12.5°	108.7
15°	103.6
17.5°	98.1
20°	91.9
22.5°	85.6
25°	79.1
27.5°	72.6
30°	66.1
32.5°	59.1
35°	52.0
37.5°	45.0
40°	38.3
42.5°	31.1
45°	24.0
47.5°	18.3
50°	13.3
52.5°	8.7
55°	6.2
57.5°	5.5
60°	5.0
62.5°	4.5
65°	4.0
67.5°	3.5
70°	3.0
72.5°	2.5
75°	2.0
77.5°	1.7
80°	1.3
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)