

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271068

Luminaire Tested: P3AS02R559827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 59.0 lumens
Efficiency: N/A
Efficacy: 16.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271068
CATALOG NUMBER: P3AS02R559827DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1271068

CATALOG NUMBER: P3AS02R559827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16051
5°	15650
10°	14540
15°	12963
20°	11014
25°	8880
30°	6761
35°	4818
40°	3177
45°	1892
50°	1092
55°	688
60°	614
65°	571
70°	449
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1892 cd/sqm



TEST NUMBER: P1271068
 CATALOG NUMBER: P3AS02R559827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.6	11.2
10°-20°	15.8	26.8
20°-30°	16.7	28.4
30°-40°	11.3	19.2
40°-50°	5.0	8.4
50°-60°	1.8	3.0
60°-70°	1.1	1.8
70°-80°	0.5	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	39.2	66.4
0°-40°	50.5	85.6
0°-60°	57.2	97.0
0°-90°	59.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	59.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	73	
5°	71	7
15°	57	16
25°	37	17
35°	18	11
45°	6	5
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1271068
CATALOG NUMBER: P3AS02R559827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	73.2
2.5°	72.6
5°	71.1
7.5°	68.6
10°	65.3
12.5°	61.4
15°	57.1
17.5°	52.2
20°	47.2
22.5°	41.9
25°	36.7
27.5°	31.6
30°	26.7
32.5°	22.1
35°	18.0
37.5°	14.3
40°	11.1
42.5°	8.3
45°	6.1
47.5°	4.5
50°	3.2
52.5°	2.3
55°	1.8
57.5°	1.6
60°	1.4
62.5°	1.2
65°	1.1
67.5°	0.9
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)