

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271078

Luminaire Tested: P3AS02R609827DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609827DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 215.0 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271078

CATALOG NUMBER: P3AS02R609827DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1271078

CATALOG NUMBER: P3AS02R609827DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51334
5°	49306
10°	50767
15°	51419
20°	45411
25°	38252
30°	31043
35°	20211
40°	9275
45°	3566
50°	1194
55°	306
60°	307
65°	259
70°	192
75°	254
80°	253
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3566 cd/sqm

TEST NUMBER: P1271078

CATALOG NUMBER: P3AS02R609827DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.6	10.0
10°-20°	62.0	28.8
20°-30°	72.3	33.6
30°-40°	46.7	21.7
40°-50°	10.5	4.9
50°-60°	1.1	0.5
60°-70°	0.5	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.9	72.5
0°-40°	202.6	94.2
0°-60°	214.1	99.6
0°-90°	215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	234	
5°	224	22
15°	226	62
25°	158	72
35°	76	47
45°	12	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1271078

CATALOG NUMBER: P3AS02R609827DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	234.1
2.5°	230.3
5°	224.0
7.5°	223.7
10°	228.0
12.5°	230.8
15°	226.5
17.5°	213.5
20°	194.6
22.5°	174.8
25°	158.1
27.5°	141.8
30°	122.6
32.5°	99.9
35°	75.5
37.5°	51.5
40°	32.4
42.5°	19.5
45°	11.5
47.5°	6.7
50°	3.5
52.5°	1.2
55°	0.8
57.5°	0.7
60°	0.7
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)