

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271901

Luminaire Tested: P3AS13R209827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 699.1 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271901

CATALOG NUMBER: P3AS13R209827DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1271901

CATALOG NUMBER: P3AS13R209827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		77
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	537808
5°	488883
10°	361316
15°	223497
20°	127644
25°	72875
30°	40867
35°	22245
40°	12166
45°	6698
50°	3923
55°	2829
60°	2675
65°	2439
70°	2180
75°	2288
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6698 cd/sqm

TEST NUMBER: P1271901

CATALOG NUMBER: P3AS13R209827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.3	27.5
10°-20°	274.6	39.3
20°-30°	143.3	20.5
30°-40°	55.4	7.9
40°-50°	18.0	2.6
50°-60°	7.1	1.0
60°-70°	4.7	0.7
70°-80°	2.8	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.2	87.3
0°-40°	665.6	95.2
0°-60°	690.7	98.8
0°-90°	699.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	699.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2453	
5°	2221	192
15°	984	275
25°	301	143
35°	83	55
45°	22	18
55°	7	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1271901

CATALOG NUMBER: P3AS13R209827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2452.6
1°	2447.8
2°	2418.8
3°	2374.2
4°	2305.4
5°	2221.0
6°	2121.0
7°	2010.3
8°	1882.0
9°	1757.0
10°	1622.7
12.5°	1289.8
15°	984.5
17.5°	736.7
20°	547.0
22.5°	405.2
25°	301.2
27.5°	222.2
30°	161.4
32.5°	116.8
35°	83.1
37.5°	60.1
40°	42.5
42.5°	30.4
45°	21.6
47.5°	15.5
50°	11.5
52.5°	8.8
55°	7.4
57.5°	6.8
60°	6.1
62.5°	5.4
65°	4.7
67.5°	4.1
70°	3.4
72.5°	3.4
75°	2.7
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)