

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271088

Luminaire Tested: P3AS02R609827DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609827DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 175.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271088

CATALOG NUMBER: P3AS02R609827DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271088

CATALOG NUMBER: P3AS02R609827DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41312
5°	40942
10°	39745
15°	37231
20°	32950
25°	27558
30°	21598
35°	15660
40°	10420
45°	6512
50°	3514
55°	1032
60°	965
65°	882
70°	833
75°	847
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6512 cd/sqm

TEST NUMBER: P1271088

CATALOG NUMBER: P3AS02R609827DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.5	10.0
10°-20°	45.5	26.0
20°-30°	51.8	29.6
30°-40°	36.8	21.0
40°-50°	16.7	9.5
50°-60°	3.5	2.0
60°-70°	1.7	1.0
70°-80°	1.1	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.9	65.6
0°-40°	151.6	86.6
0°-60°	171.9	98.2
0°-90°	175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	175.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	188	
5°	186	18
15°	164	45
25°	114	52
35°	58	37
45°	21	17
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271088

CATALOG NUMBER: P3AS02R609827DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	188.4
2.5°	187.8
5°	186.0
7.5°	182.8
10°	178.5
12.5°	172.3
15°	164.0
17.5°	153.5
20°	141.2
22.5°	127.9
25°	113.9
27.5°	99.6
30°	85.3
32.5°	71.7
35°	58.5
37.5°	46.9
40°	36.4
42.5°	27.6
45°	21.0
47.5°	15.6
50°	10.3
52.5°	4.8
55°	2.7
57.5°	2.3
60°	2.2
62.5°	2.0
65°	1.7
67.5°	1.5
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)