

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271933

Luminaire Tested: P3AS13R259827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 433.1 lumens
Efficiency: N/A
Efficacy: 29.9 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271933

CATALOG NUMBER: P3AS13R259827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271933

CATALOG NUMBER: P3AS13R259827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157202
5°	150825
10°	132128
15°	106198
20°	81604
25°	61746
30°	44614
35°	29634
40°	17977
45°	10482
50°	6686
55°	5429
60°	4736
65°	4203
70°	3462
75°	3474
80°	2526
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10482 cd/sqm

TEST NUMBER: P1271933

CATALOG NUMBER: P3AS13R259827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	14.4
10°-20°	129.4	29.9
20°-30°	117.0	27.0
30°-40°	70.3	16.2
40°-50°	27.9	6.5
50°-60°	12.9	3.0
60°-70°	7.9	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.7	71.3
0°-40°	379.0	87.5
0°-60°	419.8	96.9
0°-90°	433.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	433.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	717	
5°	685	62
15°	468	129
25°	255	117
35°	111	70
45°	34	28
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1271933

CATALOG NUMBER: P3AS13R259827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	716.9
1°	716.9
2°	713.5
3°	706.1
4°	696.7
5°	685.2
6°	670.3
7°	653.4
8°	633.9
9°	614.3
10°	593.4
11°	569.1
12°	544.1
13°	519.1
14°	494.1
15°	467.8
17.5°	405.7
20°	349.7
22.5°	299.0
25°	255.2
27.5°	214.0
30°	176.2
32.5°	141.8
35°	110.7
37.5°	84.4
40°	62.8
42.5°	45.9
45°	33.8
47.5°	25.7
50°	19.6
52.5°	16.2
55°	14.2
57.5°	12.2
60°	10.8
62.5°	8.8
65°	8.1
67.5°	6.8
70°	5.4
72.5°	4.7
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1271933

CATALOG NUMBER: P3AS13R259827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)