

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271936

Luminaire Tested: P3AS13R259827DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259827DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 390.0 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271936
CATALOG NUMBER: P3AS13R259827DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271936
 CATALOG NUMBER: P3AS13R259827DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131042
5°	123795
10°	105231
15°	83338
20°	63356
25°	47253
30°	34360
35°	24306
40°	16488
45°	11505
50°	9654
55°	9328
60°	9868
65°	10118
70°	10002
75°	10760
80°	12375
85°	12328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 13104 cd/sqm



TEST NUMBER: P1271936
 CATALOG NUMBER: P3AS13R259827DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	13.0
10°-20°	101.6	26.1
20°-30°	90.0	23.1
30°-40°	57.3	14.7
40°-50°	30.3	7.8
50°-60°	22.3	5.7
60°-70°	19.0	4.9
70°-80°	13.4	3.4
80°-90°	5.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.4	62.1
0°-40°	299.7	76.8
0°-60°	352.3	90.3
0°-90°	390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	598	
5°	562	51
15°	367	102
25°	195	90
35°	91	57
45°	37	30
55°	24	22
65°	20	19
75°	13	13
85°	5	5
90°	0	



TEST NUMBER: P1271936
CATALOG NUMBER: P3AS13R259827DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	597.6
2.5°	588.8
5°	562.4
7.5°	521.4
10°	472.6
12.5°	419.9
15°	367.1
17.5°	316.4
20°	271.5
22.5°	230.4
25°	195.3
27.5°	164.0
30°	135.7
32.5°	111.3
35°	90.8
37.5°	72.3
40°	57.6
42.5°	45.9
45°	37.1
47.5°	32.2
50°	28.3
52.5°	26.4
55°	24.4
57.5°	23.4
60°	22.5
62.5°	20.5
65°	19.5
67.5°	17.6
70°	15.6
72.5°	14.6
75°	12.7
77.5°	10.7
80°	9.8
82.5°	7.8
85°	4.9
87.5°	2.0
90°	0.0

(END OF REPORT)