

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271953

Luminaire Tested: P3AS13R309827DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309827DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 716.0 lumens
Efficiency: N/A
Efficacy: 49.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271953

CATALOG NUMBER: P3AS13R309827DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271953

CATALOG NUMBER: P3AS13R309827DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417817
5°	397666
10°	334485
15°	241227
20°	149626
25°	85094
30°	47273
35°	25698
40°	13540
45°	7350
50°	3923
55°	2600
60°	2368
65°	2439
70°	2180
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7350 cd/sqm

TEST NUMBER: P1271953

CATALOG NUMBER: P3AS13R309827DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.7	22.7
10°-20°	289.2	40.4
20°-30°	167.1	23.3
30°-40°	63.4	8.9
40°-50°	19.5	2.7
50°-60°	6.6	0.9
60°-70°	4.4	0.6
70°-80°	2.4	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.0	86.4
0°-40°	682.4	95.3
0°-60°	708.4	98.9
0°-90°	716.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	716.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1905	
5°	1807	163
15°	1063	289
25°	352	167
35°	96	63
45°	24	19
55°	7	7
65°	5	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1271953

CATALOG NUMBER: P3AS13R309827DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1905.4
1°	1904.0
2°	1892.5
3°	1870.9
4°	1843.8
5°	1806.6
6°	1759.3
7°	1706.5
8°	1647.7
9°	1577.3
10°	1502.2
11°	1421.1
12°	1335.2
13°	1245.2
14°	1153.9
15°	1062.6
17.5°	838.0
20°	641.2
22.5°	475.5
25°	351.7
27.5°	255.7
30°	186.7
32.5°	134.6
35°	96.0
37.5°	67.0
40°	47.3
42.5°	33.1
45°	23.7
47.5°	16.2
50°	11.5
52.5°	8.1
55°	6.8
57.5°	6.1
60°	5.4
62.5°	4.7
65°	4.7
67.5°	4.1
70°	3.4
72.5°	2.7
75°	2.0
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0



TEST NUMBER: P1271953
CATALOG NUMBER: P3AS13R309827DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)