

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271963

Luminaire Tested: P3AS13R309827DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309827DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 436.0 lumens
Efficiency: N/A
Efficacy: 30.1 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271963

CATALOG NUMBER: P3AS13R309827DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271963

CATALOG NUMBER: P3AS13R309827DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148979
5°	144354
10°	130058
15°	107583
20°	83307
25°	62496
30°	45374
35°	30222
40°	18578
45°	10916
50°	6686
55°	5429
60°	4736
65°	3840
70°	3462
75°	3474
80°	2526
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10916 cd/sqm

TEST NUMBER: P1271963

CATALOG NUMBER: P3AS13R309827DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	13.8
10°-20°	130.5	29.9
20°-30°	118.7	27.2
30°-40°	71.8	16.5
40°-50°	28.8	6.6
50°-60°	12.7	2.9
60°-70°	7.7	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.6	71.0
0°-40°	381.4	87.5
0°-60°	422.9	97.0
0°-90°	436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	656	60
15°	474	131
25°	258	119
35°	113	72
45°	35	29
55°	14	13
65°	7	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1271963

CATALOG NUMBER: P3AS13R309827DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	679.4
1°	678.8
2°	676.1
3°	671.3
4°	664.6
5°	655.8
6°	645.0
7°	633.5
8°	618.6
9°	601.7
10°	584.1
11°	563.8
12°	542.2
13°	520.6
14°	496.9
15°	473.9
17.5°	413.8
20°	357.0
22.5°	304.2
25°	258.3
27.5°	216.3
30°	179.2
32.5°	144.7
35°	112.9
37.5°	86.5
40°	64.9
42.5°	47.3
45°	35.2
47.5°	26.4
50°	19.6
52.5°	15.5
55°	14.2
57.5°	12.2
60°	10.8
62.5°	8.8
65°	7.4
67.5°	6.8
70°	5.4
72.5°	4.7
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1271963
CATALOG NUMBER: P3AS13R309827DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)