

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271148

Luminaire Tested: P3AS02R709827DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709827DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 168.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271148

CATALOG NUMBER: P3AS02R709827DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271148

CATALOG NUMBER: P3AS02R709827DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77		
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70		
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32519
5°	32137
10°	31195
15°	29875
20°	28002
25°	25429
30°	21978
35°	17507
40°	12738
45°	8373
50°	3923
55°	1223
60°	1184
65°	1141
70°	1090
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8373 cd/sqm

TEST NUMBER: P1271148

CATALOG NUMBER: P3AS02R709827DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.7	8.2
10°-20°	36.8	21.9
20°-30°	47.9	28.5
30°-40°	40.6	24.2
40°-50°	20.9	12.5
50°-60°	4.0	2.4
60°-70°	2.2	1.3
70°-80°	1.3	0.8
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.5	58.6
0°-40°	139.1	82.8
0°-60°	164.1	97.7
0°-90°	168.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	168.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	148	
5°	146	14
15°	132	37
25°	105	48
35°	65	41
45°	27	21
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271148

CATALOG NUMBER: P3AS02R709827DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	148.3
2.5°	147.8
5°	146.0
7.5°	143.3
10°	140.1
12.5°	136.1
15°	131.6
17.5°	126.1
20°	120.0
22.5°	112.9
25°	105.1
27.5°	96.3
30°	86.8
32.5°	76.2
35°	65.4
37.5°	54.7
40°	44.5
42.5°	35.0
45°	27.0
47.5°	19.9
50°	11.5
52.5°	5.0
55°	3.2
57.5°	3.0
60°	2.7
62.5°	2.5
65°	2.2
67.5°	2.0
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)