

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271975

Luminaire Tested: P3AS13R359827DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359827DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 858.1 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271975

CATALOG NUMBER: P3AS13R359827DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271975

CATALOG NUMBER: P3AS13R359827DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	559473
5°	548073
10°	509877
15°	373827
20°	191420
25°	68980
30°	26865
35°	9396
40°	3864
45°	1054
50°	921
55°	1032
60°	877
65°	726
70°	898
75°	1186
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1186 cd/sqm

TEST NUMBER: P1271975

CATALOG NUMBER: P3AS13R359827DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	27.1
10°-20°	435.5	50.8
20°-30°	154.2	18.0
30°-40°	27.0	3.1
40°-50°	4.0	0.5
50°-60°	2.2	0.3
60°-70°	1.6	0.2
70°-80°	1.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	821.8	95.8
0°-40°	848.8	98.9
0°-60°	855.0	99.6
0°-90°	858.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2551	
5°	2490	232
15°	1647	436
25°	285	154
35°	35	27
45°	3	4
55°	3	2
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271975

CATALOG NUMBER: P3AS13R359827DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2551.4
1°	2550.7
2°	2542.6
3°	2527.1
4°	2512.9
5°	2489.9
6°	2466.3
7°	2439.9
8°	2407.5
9°	2356.8
10°	2289.9
11°	2197.3
12°	2085.9
13°	1953.4
14°	1807.5
15°	1646.7
17.5°	1226.4
20°	820.3
22.5°	494.6
25°	285.1
27.5°	170.3
30°	106.1
32.5°	61.5
35°	35.1
37.5°	22.3
40°	13.5
42.5°	6.8
45°	3.4
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.0
60°	2.0
62.5°	2.0
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1271975

CATALOG NUMBER: P3AS13R359827DE010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)