

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271154

Luminaire Tested: P3AS02R709827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 120.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271154

CATALOG NUMBER: P3AS02R709827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271154

CATALOG NUMBER: P3AS02R709827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28156
5°	27625
10°	26052
15°	23655
20°	20675
25°	17445
30°	14281
35°	11082
40°	7929
45°	5024
50°	2490
55°	1529
60°	1316
65°	1193
70°	1090
75°	1017
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5024 cd/sqm

TEST NUMBER: P1271154

CATALOG NUMBER: P3AS02R709827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.7	9.8
10°-20°	29.0	24.2
20°-30°	33.0	27.5
30°-40°	25.8	21.5
40°-50°	12.7	10.6
50°-60°	3.9	3.2
60°-70°	2.3	1.9
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	73.7	61.4
0°-40°	99.5	82.9
0°-60°	116.1	96.7
0°-90°	120.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	120.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	128	
5°	126	12
15°	104	29
25°	72	33
35°	41	26
45°	16	13
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271154

CATALOG NUMBER: P3AS02R709827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	128.4
2.5°	127.7
5°	125.5
7.5°	122.0
10°	117.0
12.5°	111.2
15°	104.2
17.5°	96.6
20°	88.6
22.5°	80.3
25°	72.1
27.5°	64.1
30°	56.4
32.5°	48.7
35°	41.4
37.5°	34.4
40°	27.7
42.5°	21.5
45°	16.2
47.5°	11.4
50°	7.3
52.5°	4.8
55°	4.0
57.5°	3.5
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.3
75°	1.2
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)